

Designed by Komplot Design

PRODUCT



COLOURS



Item no.: 21001-3A-01 + style code

DESCRIPTION

The GUBI Chair Collection is a chair series in laminated moulded 3-D veneer or in the injection moulded plastic material. The shell is 5 mm thick. Both types of the shells can be delivered upholstered, with front upholstered or fully upholstered in fabric or leather. The base is available in steel, in different finishes as specified below and moulded wood in various finishes. Several of the chair versions are stackable. The GUBI Chair series includes a side chair with and without arms, a bar stool, a lounge chair and a table series in 3 different heights.

VERSION - PLASTIC

RAL codes are indicative.

- Black // RAL 9005, silkmatt /
- Venetian Gold // RAL 080 7050 , silkmatt /
- Mistletoe Green // RAL 130 5010, silkmatt /
- Nightfall Blue // RAL 200 7005, silkmatt /
- Rainy Gray // RAL 7031, silkmatt /
- White Cloud // RAL 9001, silkmatt /
- Moon Gray // RAL 085 7010, silkmatt /
- Shy Cherry // RAL 3011, silkmatt /
- Chrome base // -
- Satin chrome base // -
- Black painted base // RAL 9005, gloss level 10-15


CHAIR VERSION

14-09-2016

Order item - look for part number in the pricelist.

The series consists of the following:

GUBI 3A, GUBI 32A, GUBI 33A



FACTS

MEASUREMENT - L X W X H MM

Sitting height: 650 mm Seat width: 401 mm Seat depth: 416 mm Seat height: 147 mm

Back height: 163 mm Frame width: 441 mm Frame depth: 447 mm

Chair height: 775 mm Shell thickness: 5 mm

Frame thickness: Ø11 mm Footrest height: 200 mm

PACKAGING TYPE Cardboard box

WEIGHT ITEM 4,880 kg

PACKAGING MEASUREMENT - L X W X H CM L:44 X W:44 X H:80 CM

WEIGHT PACKAGING - MATERIAL TYPE

- Delivery note: 5 g
- Cardboard box, FEFCO quality EB85BB: 1485 g
- Cardboard extra bottom: 272 g
- Polybag PE: 158 g
- LD-EPE foam protector: 44 g
- Strapping: 7 g

WEIGHT PACKAGING - *TOTAL* 6,851 kg

NUMBER OF PARCELS

1 pcs.

- Defective frame and shells can be replaced.



ACCESSORIES

FELT GLIDERS FOR HARD FLOOR AVAILABLE ON REQUEST.

LINKING DEVICE



CLEANING AND MAINTENANCE

For dusting and light cleaning of the plastic surface and frame use a soft, dry cloth.

For further cleaning, use a soft cloth that is firmly wrung in clean water for gently wiping the surface, and then immediately use a dry cloth to wipe the surface again.

If more thorough cleaning is necessary, use a mild detergent or washing-up liquid dissolved in water on a firmly wrung cloth. Afterwards, repeat the process with clean water as described above. Polish with a soft cloth after wiping.

Do not use materials for maintenance that:

- · Contain abrasive agents.
- Are basic, acidiferous or organic.

For the best maintenance of the product, protect it against sunlight and heat, and try to keep it away from moisture, grease and other dirt.

Furthermore, protect the surfaces against sharp objects and other that might scratch.

ENVIRONMENT

Parts can be separated and sorted for recycling.

Disposal of plastic type PP may be done with incineration of waste.

TESTS

-

CERTIFICATION AND LABELS

-